

Element Materials Technology 3922 Delaware Avenue Des Moines, IA 50313-2542 USA P 515 266 5101 F 515 262 1910 T 888 786 7566 info.desmoines@element.com element.com

Impact Testing of Organic coated Glass in accordance with ANSI Z97.1-2009, CAN/CSGB-12.1-M90 and CPSC 1201

3M Renewable Energy Attn: Paul Neumann 3M Center, 235-3D-02 St. Paul, MN 55144 Date: August 20, 2014
Author: Josh Garrison
Report Number: ESP016970P.2

3M SCOTCHSHIELD Ultra 800

It is our policy to retain components and sample remnants for a minimum of 30 days from the report date, after which time they may be discarded. The data herein represents only the item(s) tested. This report shall not be reproduced, except in full, without prior permission of Element Materials Technology.

EAR Controlled Data: This document contains technical data whose export and re-export/retransfer is subject to control by the U.S. Department of Commerce under the Export Administration Act and the Export Administration Regulations. The Department of Commerce's prior written approval may be required for the export or re-export/retransfer of such technical data to any foreign person, foreign entity or foreign organization whether in the United States or abroad.

This project shall be governed exclusively by the General Terms and Conditions of Sale and Performance of Testing Services by Element Materials Technology. In no event shall Element Materials Technology be liable for any consequential, special or indirect loss or any damages above the cost of the work.

This certificate shall not be reproduced, except in full, without the written approval of the laboratory.

Element Materials Technology 3922 Delaware Avenue Des Moines, IA 50313-2542 USA P 515 266 5101 F 515 262 1910 T 888 786 7566 info.desmoines@element.com

EAR-CONTROLLED DATA

INTRODUCTION:

The following report presents the results of impact testing of organic coated glass in accordance with the ANSI Z97.1-2009, National Standard of Canada CAN/CGSP-12.1-M90 and CPSC 1201 standards. Testing was requested by Paul Neumann of 3M Renewable Energy. The samples were received on June 4, 2014 and testing was completed by Josh Garrison on June 23, 2014.

SUMMARY OF RESULTS:

3M Scotchshield Ultra 800 film when applied to nominal 1/4" annealed glass **Complies** with the safety glazing impact requirements of ANSI Z97.1-2009, CAN/CSGB-12.1-M90 and CPSC 1201.

3M Scotchshield Ultra 800 film when applied to nominal 1/8" annealed glass **Complies** with the safety glazing impact requirements of ANSI Z97.1-2009, CAN/CSGB-12.1-M90 and CPSC 1201.

TEST METHODS AND RESULTS:

Impact Test

Specimens were kept at a temperature of 70-80° F for a minimum of four hours preceding the test. Specimens were impacted alternating on the film side and the glass side, as noted in the tables in the following results section. Each specimen was struck once within ½ inch of center, with a shot bag constructed in accordance with the specifications referenced, swinging in a pendulum arc, from a drop height shown below.

3M Scotchshield Ultra 800 8 Mil – 1/4" Annealed Glass										
Sample Identification	Impact Side	Total Thickness Inches	Drop Height Inches	Weight of All Lost Particles (grams)	Weight of Largest Piece (grams)	Results/Size of Opening				
#1	Film	0.229	48	408	17	Pass – No tears / No openings				
#2	Glass	0.229	48	346	12	Pass – 14" vertical tear, Sphere would not pass through.				
#3	Film	0.227	48	295	11	Pass – No tears / No openings				
#4	Glass	0.230	48	171	4	Pass – No tears / No openings				

Element Materials Technology 3922 Delaware Avenue Des Moines, IA 50313-2542 USA P 515 266 5101 F 515 262 1910 T 888 786 7566 info.desmoines@element.com element.com

EAR-CONTROLLED DATA

3M Scotchshield Ultra 800 8 Mil – 1/8" Annealed Glass										
Sample Identification	Impact Side	Total Thickness Inches	Drop Height Inches	Weight of All Lost Particles (grams)	Weight of Largest Piece (grams)	Results/Size of Opening				
#1	Film	0.133	48	103	3	Pass – No tears / No openings				
#2	Glass	0.132	48	170	12	Pass – No tears / No openings				
#3	Film	0.133	48	134	1	Pass – No tears / No openings				
#4	Glass	0.133	48	339	7	Pass – No tears / No openings				

CALIBRATED TEST EQUIPMENT:

PT-173-032 Starrett Micrometer
 PT-173-018 Sartorius Scale
 Calibration Due: 11/07/2014
 Calibration Due: 09/04/2014

PT-177-012 Tape Measure Calibration Due: 02/07/2018

DISPOSITION OF SAMPLE:

Samples were destroyed during testing and were disposed of immediately.

Prepared by:

Josh Garrison

Product Evaluation Technician

Reviewed by:

Brian S. Escherich Operations Manager